



Medical Equipment Washing and Decontamination Systems

## AQ-3500

### Features

**Aqua Phase Model AQ-3500** is designed for larger chairs. The AQ-3500 wash chamber can easily accommodate most larger chairs as well as standard wheelchairs, walkers, stands etc. It is designed and built to handle the heavy washing requirements of large long term care facilities, large home medical and durable medical equipment dealers, and hospitals.

The AQ-3500 with the Disinfection Application System will be an integral part of your infection control protocols. Some units of Model AQ-3500 have had tens of thousands of cycles ran through them and are still going strong. AQ-3500 features double wall Stainless Steel construction to act as a heat insulator. The AQ-3500 is mounted on four large, durable casters to allow for easy relocation and The AQ-3500 comes standard with the Disinfection Application System, the Wheel Rotation System for wheelchair wheels and Safety Glass Window.

One of the key additional standard features of the AQ-3500 is the wall mounted studs. This allows you, now or in the future, to order the Utility Wash Trays System. More importantly, it allows you to customise your own racking system to handle your specific wash needs.

### Standard Features - AQ-3500:

- Stainless Steel Construction and Spray Arms
- Double Walled
- Disinfectant Application System
- Front Door Safety Glass Window
- Variable Wash Time Cycles (3, 5, or 7 minute)
- Rinse Cycle System
- Rotation of Wheelchair Wheels (Front & Rear)
- Heavy Duty Casters
- Hot Water Hose Set (Set of 2 – 3m)
- Oscillating steel spray arms



### Options – AQ-3500:

- Equipment Loading Wash Rack
- Utility Wash Trays
- Electronic Temperature Monitor
- Lighted Wash Chamber
- Air Dry Blower
- Utility Chamber Floor
- Multi-Size Wheel Rotator
- Special Time Cycles
- 220 Volt 50/60 Hz Operation
- Long Hot Water Hose Set (Set of 2 – 7.5m)



### Design Features - AQ-3500:

Construction (Stainless Steel)	Double Walled
System Controls Are By	Logic Controller
Spray Arm Assemblies	Stainless Steel
Tested to European Specs.	Yes
UL Listed Electronics Assembly	Standard
Rinse Cycle	Standard
Cleaner Injection System	Peristaltic
Wash Cycle Lengths	3,5 or 7 minutes
Disinfectant Application (Optional)	Automatic
Filter Clogging Signal	Standard
Water Level Sensor	Electronic
GFCI Breaker in Power Cord	Standard
Safety Switch Front & Rear	Standard
Maximum AMP Draw	12.6
Warranty - Wash Chamber	5 Years
Warranty – Parts	1 Year
Country of Manufacture	USA



### Dimensions - AQ-3500:

Machine Outside Width	1257 mm
Machine Outside Length	1931 mm
Machine Outside Height	1854 mm
Wash Chamber Width	1022 mm
Wash Chamber Height	1432 mm
Wash Chamber Length	1435 mm
Shipping Weight	658 kg

**Aqua Phase**

sales@aquaphase.com.au

http://www.aquaphase.com.au